






Outer shell	: Aluminium (AA 6262A) or (AA 6023) Anthracite nickel
Earthing crown+gland	: Brass (UNS C38500)+Fluorosilicone (FVMQ) Gold plated (ISO 27874)
Insulator	: PEEK
Male contacts ($\phi 0.7 + \phi 1.3$)	: Brass (UNS C38500) Gold plated (ISO 27874)
O-ring	: Viton (FPM)

PCB drilling pattern



Panel cut-out



Fixed socket , square flange , with keys (X) ,
4 holes fixing , for PCB .
Series 5M , multipole 44LV($\phi 0.7$) + 22LV($\phi 1.3$)

ETUDE N° E6367-E4282

Echelle —	Dessiné	06.09.2018	OVU / NHA
	Contrôle	06.09.2018	NHA / ATVI
	Modif.	00	06.09.2018/ OVU



LEMO

LEMO SA
Chemin des Champs-Courbes 28
1024 Ecublens - SWITZERLAND

Tel. (+41 21) 695 16 00
email : info@lemo.com
www.lemo.com

EDX.5M.366.XRY44