



Outer shell	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Earthing crown	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)
Insulator	: PEEK	-
Female contact	: Bronze (UNS C54400)	Gold plated (ISO 27874)
Clip	: Cu-Be (UNS C17200)	-
Notched nut	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Other metallic part	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)
O-rings	: Silicone (MVQ)	-
Contact wire	: Brass (UNS C27400)	Tinned
Position insert	: FEP	-

<p>Panel cut-out</p> <p>Torque for mounting nut : 9 Nm</p>	<p>A-A cross-section (PCB drilling pattern)</p>	<p>Spanner for notched nut : DCH.91.251.PA</p>
--	---	--

Fixed socket , nut fixing , with keys (C) , with elbow (90°) contact for PCB . (Back panel mounting) . Series 2K , multipole (10)

ETUDE N° E6296

Echelle	Dessiné	06.06.2017	OVU / NHA
	Contrôle	06.06.2017	NHA / ATVI
	Modif.	00	06.06.2017/ OVU



EEC.2K.310.CLV