






Outer shell	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Earthing crown	: Bronze (UNS C54400)	Nickel plated (FS-QQ-N-290A)
Insulator	: PEEK	-
Female contact	: Bronze (UNS C54400)	Gold plated (ISO 4523)
Locking washer	: Bronze (UNS C52100)	Nickel plated (FS-QQ-N-290A)
Other metallic parts	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)

Panel cut-out



Torque for
mounting
nut : 9 Nm

Spanner for nut : DCA.91.282.2TN or
Spanner for nut : DCG.91.282.2TN

Fixed socket with nut fixing , with key (G) .
Series 3B , multipole (16)

ETUDE N°

Echelle

—

Dessiné	01.02.07	OVU / RMO
Contrôle	01.02.07	RMO / CDE
Modif.	00	01.02.07 / OVU



LEMO

CH-1024 Ecublens

EGG.3B.316.CLL