



Collet : Brass (UNS C38500) Nickel plated (FS-QQ-N-290A)

REFERENCE	Note	ϕ Collet (mm)		ϕ Cable (mm)		L	Nb Slots
		ϕA	ϕB	max.	min.		
FFA.0S.722.CNT		2,2	2,2	2,2	1,3	10.5	4
FFA.0S.732.CNT		3,2	3,2	3,2	2,3	10.5	4
FFA.0S.737.CNT		3,7	3,7	3,7	3,3	10.5	4
FFA.0S.744.CNT	1)	4,4	3,7	4,4	3,8	10.2	4

Note : 1) Collet nut to use : FFA.0S.131.LC

Collet . (Transient reference)
Series 0S

ETUDE N° E7209

Echelle —	Dessiné	18.01.2016	OVU / NHA
	Contrôle	18.01.2016	NHA / ATVI
	Modif.	00	18.01.2016 / OVU



LEMO

CH-1024 Ecublens

FFA.0S.7___.CNT