



Collet

: Brass (UNS C38500)

Nickel plated (FS-QQ-N-290A)

REFERENCE	Note	φ Collet (mm)		φ Cable (mm)		L	Nb Slots
		φA	φB	max.	min.		
FFA.1S.722.CNT		2,2	3,2	2,2	1,4	12.5	4
FFA.1S.732.CNT		3,2	3,2	3,2	2,3	12.5	4
FFA.1S.742.CNT		4,2	4,2	4,2	3,3	12.5	4
FFA.1S.752.CN	2)			5,2	4,3		
FFA.1S.757.CNT	1)	5,7	5,2	5,7	5,3	12.3	4
FFA.1S.762.CNT	1)	6,2	5,2	6,2	5,8	12.3	4

Note : 1) Collet nut to use : FFA.1S.131.LC

Note : 2) See customer drawing : FFA.1S.7___.CN

Collet . (Transient reference)
Series 1S

Echelle —	Dessiné	30.11.2017	OVU / NHA
	Contrôle	30.11.2017	NHA / ATVI
	Modif.	00	30.11.2017 / OVU

ETUDE N° E7210



LEMO

LEMO SA
Chemin des Champs-Courbes 28
1024 Ecublens - SWITZERLAND

Tel. (+41 21) 695 16 00
email : info@lemo.com
www.lemo.com

FFA.1S.7___.CNT