



Collet : Brass (UNS C38500) Nickel plated (FS-QQ-N-290A)

REFERENCE	Note	φ Collet (mm)		φ Cable (mm)		L	Nb Slots
		φ A	φ B	max.	min.		
FGG.0B.722.DN		2,2	4,2	2,2	1,4	9.0	4
FGG.0B.732.DN		3,2	4,2	3,2	2,3	9.0	4
FGG.0B.742.DN		4,2	4,2	4,2	3,3	9.0	6
FGG.0B.752.DN		5,2	4,7	5,2	4,3	8.7	6
FGG.0B.756.DN	1) 2)	5,6	4,7	5,6	5,3	8.4	6

Note : 1) Can not be used with collet nut for bend relief .  
 Note : 2) Collet nut to use : FGG.0B.131.LC

Collet . (New design)  
 Series 0B

ETUDE N° E6040-E7195

Echelle —	Dessiné	30.10.1998	OVU / JCHU
	Contrôle	10.02.2014	JPBA / ATVI
	Modif.	04	10.02.2014 / OVU



**LEMO**

CH-1024 Ecublens

**FGG.0B.7\_\_\_.DN**