



Collet : Brass (UNS C38500) Nickel plated (FS-QQ-N-290A)

REFERENCE	Note	φ Collet (mm)		φ Cable (mm)	
		φA	φB	max.	min.
FGG.1B.742.DN		4,2	4,2	4,2	3,1
FGG.1B.752.DN		5,2	5,6	5,2	4,3
FGG.1B.762.DN		6,2	6,6	6,2	5,3
FGG.1B.772.DN	3)	7,2	6,7	7,2	6,3
FGG.1B.776.DN	1) 2)	7,6	6,7	7,6	7,3

Note : 1) Can not be used with collet nut for bend relief .
 Note : 2) Collet nut to use : FGG.1B.132.LC
 Note : 3) Collet nut to use : FGG.1B.131.LC

Collet . (New design)
 Series 1B

ETUDE N° E6040-E7195

Echelle —	Dessiné	17.04.1997	LMO / JCHU
	Contrôle	14.03.2013	JPBA/ATVI
	Modif.	05	14.03.2013/ OVU



LEMO

CH-1024 Ecublens

FGG.1B.7___.DN