



Collet

: Brass (UNS C38500)

Nickel plated (FS-QQ-N-290A)

REFERENCE	Note	φ Collet (mm)		φ Cable (mm)	
		φA	φB	max.	min.
FGG.2B.742.DN		4,2	7,2	4,2	3,2
FGG.2B.752.DN		5,2	5,2	5,2	4,3
FGG.2B.762.DN		6,2	6,2	6,2	5,3
FGG.2B.772.DN		7,2	7,2	7,2	6,3
FGG.2B.782.DN		8,2	8,2	8,2	7,3
FGG.2B.792.DN		9,2	8,6	9,2	8,3
FGG.2B.799.DN	1) 2)	9,9	8,6	9,9	9,3

Note : 1) Can not be used with collet nut for bend relief .

Note : 2) Collet nut to use : FGG.2B.132.LC

Collet . (New design)
Series 2B

ETUDE N° E6040-E7195

Echelle

—

Dessiné

17.04.1997

LMO / JCHU

Contrôle

13.01.2012

JPBA/ ATVI

Modif.

04

13.01.2012/ OVU



LEMO

CH-1024 Ecublens

FGG.2B.7___.DN