



Outer shell	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Latch sleeve	: Special brass	Chrome plated (FS-QQ-C-320B)
Inner shell	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)
Collet nut	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Insulator	: PEEK	-
Male contact (LV)	: Brass (UNS C38500)	Gold plated (ISO 27874)
Clip	: Bronze (UNS C54400)	Nickel plated (FS-QQ-N-290A)
Other metallic parts	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)
O-ring	: Silicone (MVQ)	-
Bend relief	: Polyurethane	Various colors

Parts that must be ordered separately :
 Fiber-optic contact ref : FFS.F7.125.LCE23 ferrule hole 125µm
 Fiber-optic contact ref : FFS.F7.126.LCE23 ferrule hole 126µm
 Bend relief réf : GMA.2B.060.D__

Assembly instruction per document n° __

**Straight plug , with key (G) , cable collet adapter
 and nut for fitting a bend relief .**

Series 2K , 2FO(typeF7) + 4LV(φ0.7)

ETUDE N° E6041-E7182-E9938-E7073

Echelle	Dessiné	06.01.2017	OVU / NHA
	Contrôle	06.01.2017	NHA / ATVI
	Modif.	00	06.01.2017/ OVU



LEMO

CH-1024 Ecublens

FGG.2K.93B.CLAT66Z