



Outer shell	: Stainless steel (AISI303)	-
Latch sleeve	: Special brass	Chrome plated (FS-QQ-C-320B)
Inner shell	: Stainless steel (AISI303)	-
Collet nut	: Stainless steel (AISI303)	-
Insulator	: PEEK	-
Other metallic parts	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)
O-ring	: Viton (FPM)	-
Bend relief	: Polyurethan	Various colors

Parts that must be ordered separately :
 Fiber-optic contact ref : FFS.F7.125.LCL23 ferrule hole 125 μ m
 Fiber-optic contact ref : FFS.F7.126.LCL23 ferrule hole 126 μ m
 Bend relief réf : GMA.3B.070.D__

Assembly instruction per document n° __

**Straight plug , with key (G) , cable collet adapter
 and nut for fitting a bend relief .
 Series 4K , 8FO(typeF7)**

ETUDE N° E2890

Echelle —	Dessiné	30.11.05	OVU / RMO
	Contrôle	30.11.05	RMO / CDE
	Modif.	00	30.11.05 / OVU



LEMO

CH-1024 Ecublens

FGG.4K.03G.SLZT76Z