



| | | |
|----------------------|----------------------|------------------------------|
| Outer shell | : Brass (UNS C38500) | Chrome plated (FS-QQ-C-320B) |
| Latch sleeve | : Special brass | Chrome plated (FS-QQ-C-320B) |
| Inner shell | : Brass (UNS C38500) | Nickel plated (FS-QQ-N-290A) |
| Collet nut | : Brass (UNS C38500) | Chrome plated (FS-QQ-C-320B) |
| Insulator | : PEEK-PDX-L-97024 | - |
| Other metallic parts | : Brass (UNS C38500) | Nickel plated (FS-QQ-N-290A) |
| O-Ring | : FPM | - |
| Bend relief | : Polyurethan | Various colors |

Parts that must be ordered separately :
 Fiber-optic contact ref : FFS.F2.BA2.LCE30 ferrule hole 125µm
 Bend relief ref : GMA.4B.011.D__

Assembly instruction per document n° __

**Straight plug , with key (G) , cable adapter
 and nut for fitting a bend relief .
 Series 5K , 10FO(typeF2)**

ETUDE N°

| | | | |
|--------------|----------|------------|-----------------|
| Echelle — | Dessiné | 26.03.2001 | OVU / RMO |
| | Contrôle | 26.03.2001 | RMO / CDE |
| | Modif. | 00 | 26.03.2001/ OVU |



LEMO

CH-1024 Ecublens

FGG.5K.03J.CLZT11Z