



Outer shells	: Aluminium (AA 6262A) or (AA 6023) Anthracite nickel
Latch nut	: Aluminium (AA 6262A) or (AA 6023) Anthracite nickel
Insulator	: PEEK
Ratchets	: PEEK-Carbon
Grommet	: Fluorosilicone (FVMQ)
Female contacts ($\phi 0.7 + \phi 1.3$)	: Bronze (UNS C54400)
Clip	: Cu-Be (UNS C17200)
Clip + Spring	: Stainless steel
Other metallic part	: Brass (UNS C38500)

Crimping tool	: DPC.91.701.V
Extractor	: DCF.93.070.4LT
Female contact ($\phi 0.7$)	: EGW.TM.655.ZZM
Female positioner	: DCE.91.07T.5MVM
Female retention testing tool	: DCK.91.071.0LRM
Female insertion tool	: DCV.07.05M.LA
Crimping tool	: DPC.91.701.V
Extractor	: DCF.93.131.4LT
Female contact ($\phi 1.3$)	: EGN.0M.667.ZZM
Female positioner	: DCE.91.130.5MVU
Female retention testing tool	: DCK.91.132.5LRM
Female insertion tool	: DCV.13.05M.LA

**Straight plug , with keys (X) ,
with artic grip and mold stop .
Series 5M , multipole 44LV($\phi 0.7$) + 22LV($\phi 1.3$)**

ETUDE N° E6367-E6364-E4282

Echelle —	Dessiné	20.09.2018	OVU / NHA
	Contrôle	09.09.2019	NHA / ATVI
	Modif.	01	09.09.2019/ OVU



LEMO

LEMO SA
Chemin des Champs-Courbes 28
1024 Ecublens - SWITZERLAND

Tel. (+41 21) 695 16 00
email : info@lemo.com
www.lemo.com

FGX.5M.366.XRYT44