



Outer shell	: Stainless steel (AISI304)	-
Latch sleeve	: Stainless steel (AISI416)	-
Inner sleeve	: Stainless steel (AISI304)	-
Front ring	: Stainless steel (AISI304)	-
Collet nut + clamps + screw	: Stainless steel (AISI304)	-
Insulator	: PEEK	-
Male contact	: Brass (UNS C38500)	Gold plated (ISO 4523)
Clip	: Stainless steel (AISI416)	-
Gland	: EPDM	-
Lanyard release	: Stainless steel (AISI316)	-
Other outer metallic parts	: Stainless steel (AISI304)	-
Other inner metallic parts	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)
O-rings	: EPDM	-
Marking strip	: Epoxy paint	black

**Elbow plug (120°) with positioning pin , with cable clamps
rough narrow handling surface and with lanyard release .
Series 5N , multipole (20)**

ETUDE N° E6225

Echelle

Dessiné

12.06.98

FNI /ATAB

Contrôle

22.08.02

RMO / CDE

Modif.

01

22.08.02 / OVU



LEMO

CH-1024 Ecublens

FMG.5N.320.TLAY22