







Outer shell	: Aluminium (AA 6262A) or (AA 6023)	Anthracite nickel
Earthing crown	: Bronze (UNS C54400)	Nickel plated (FS-QQ-N-290A)
Insulator	: PEEK	-
Male contact	: Brass (UNS C38500)	Gold plated (ISO 4523)
Conical nut	: Aluminium (AA 6262A) or (AA 6023)	Red anodized
Ground pin	: Stainless steel (AISI303)	Gold plated (ISO 4523)
Sealing resin	: Epoxy	-
O-ring	: Silicone (MVQ)	-

Panel cut-out



Torque for
mounting
nut : 2.5 Nm

PCB drilling pattern



**Fixed socket , nut fixing , with keys (S)
watertight , for PCB . (Back panel mounting) .
Series 3F , multipole (30)**

ETUDE N° E6213-E2704

Echelle

Dessiné 25.04.2007 OVU / RMO

Contrôle 07.09.2011 JPBA/ATVI

Modif. 01 07.09.2011/ OVU



LEMO

CH-1024 Ecublens

HES.3F.330.XLDPS