



Outer shell	: Brass (UNS C38500)	Chrome plated (SAE AMS 2460)
Earthing crown	: Brass (UNS C38500)	Nickel plated (SAE AMS QQ N 290)
Retaining ring	: Stainless steel (AISI304L)	-
Collet nut	: Brass (UNS C38500)	Chrome plated (SAE AMS 2460)
Insulator	: PEEK	-
Other metallic parts	: Brass (UNS C38500)	Nickel plated (SAE AMS QQ N 290)
O-rings	: Silicone (MVQ)	-
Bend relief	: Polyurethan	Various colors

Parts that must be ordered separately :
 Fiber-optic contacts refs : PSS.F1.xxx.Axx ___
 Bend relief réf : GMA.2B.050.D_

Assembly instruction per document n° ___

**Free socket , with key (G) , cable collet adapter
 and nut for fitting a bend relief .**

Series 3K , 2FO(typeF1)

ETUDE N° E7077-E7182-E6041-E2328-E7073

Echelle —	Dessiné	16.12.2020	OVU / NHA
	Contrôle	16.12.2020	NHA / CDE
	Modif.	00	16.12.2020 / OVU



LEMO

LEMO SA
 Chemin des Champs-Courbes 28
 1024 Ecublens - SWITZERLAND

Tel. (+41 21) 695 16 00
 email : info@lemo.com
 www.lemo.com

PHG.3K.07A.CLZT56Z