





Note: Minimum length of the thread to ensure mating with plug FVB


Outer shell	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)
Earthing crown	: Bronze (UNS C54400)	Nickel plated (FS-QQ-N-290A)
Insulators	: PEEK	-
Female contact	: Bronze (UNS C54400)	Gold plated (ISO 4523)
Special notched nut	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)
Screw	: Steel	Zinc plated
Other metallic part	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)

Panel cut-out



Torque for
mounting
nut : 1 Nm

A-A cross-section (PCB drilling pattern)



(x) For screw M1.4x0.3 tightening torque value : 6 to 7 Ncm

Spanner for notched nut : DCB.91.455.0LN

**Elbow socket (90°) with special notched nut , with keys (B) ,
for PCB . (Back panel mounting) .
Series 00 , multipole (3)**

ETUDE N° E1957

Echelle

—

Dessiné	07.04.95	OVU / GJE
Contrôle	15.04.09	JPBA/ CDE
Modif.	04	15.04.09 / OVU



LEMO

CH-1024 Ecublens

XRB.00.303.NLN