

# T series

The FSG model for the T series is a new right angled «Anglissimo» connector. The connector is sealed to IP68 and is ideal for use in outside environment.

The T series Anglissimo connector has a specific feature where the position of the cable can be pre-positioned at various angles during the initial cable assembly in one of the 8 positions. By preventing any cable clutter, this connector solution enables easy access to complex cable panels.

Finally a wide choice of blanking caps from the T series (both plug and socket) completes this range of connector.

#### Features:

- -8 in 1 plug
- IP 68
- Cable clarity
- Clean design
- Reduce operating failures caused by stressed cables






### Model


## FS. Adjustable right angle plug





Reference		Dimensions (mm)					
Model	Series	Α	Н	L	М	S1	S2
FSG	TT	8	20.0	28.5	20.5	5	7.5
FSG	0T	10	23.0	36.0	26.0	7	9.5
FSG	1T	13	30.0	43.5	32.5	9	12.0
FSG	2T	17	37.5	54.0	42.0	12	16.0

**Note:** • = alignment key. See T series catalogue.



For insert types and collet sizes see T series catalogue: https://www.lemo.com/catalog/ROW/UK\_English/T\_series\_en.pdf

# LEMO HEADQUARTERS

SWITZERLAND

Chemin des Champs-Courbes 28 - P.O. Box 194 - CH-1024 Ecublens
Tel. (+41 21) 695 16 00 - e-mail: info@lemo.com

## www.lemo.com