







Outer shell	: Brass (UNS C38500)	Chrome plated (SAE AMS 2460)
Earthing crown	: Bronze (UNS C54400)	Nickel plated (SAE AMS QQ N 290)
Male sleeve with tag	: Brass (UNS C34500)	Gold plated (ISO 27874)
Insulators	: PTFE	-
Female contact	: Bronze (UNS C54400)	Gold plated (ISO 27874)
Earthing tag	: Brass (UNS C38500)	Gold plated (ISO 27874)
Notched nut	: Brass (UNS C38500)	Chrome plated (SAE AMS 2460)
O-rings	: Silicone (MVQ)	-

Panel cut-out



Torque for
mounting
nut : 5 Nm

PCB drilling pattern



Spanner for notched nut : DCH.91.181.PA

**Fixed socket , with nut fixing ,
for PCB . (Back panel mounting) .
Series 0E , triaxial (50Ω)**

ETUDE N° E10927-E1834-E1241-E10630-E4046-E1120-E10721

Echelle

Dessiné	18.05.2020	OVU / NHA
Contrôle	18.05.2020	NHA / CDE
Modif.	00	18.05.2020/ OVU



LEMO

LEMO SA
Chemin des Champs-Courbes 28
1024 Ecublens - SWITZERLAND

Tel. (+41 21) 695 16 00
email : info@lemo.com
www.lemo.com

EAP.0E.650.CTN