







Outer shell	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Earthing crown	: Bronze (UNS C54400)	Nickel plated (FS-QQ-N-290A)
Insulator	: PEEK	-
Female contact	: Bronze (UNS C54400)	Gold plated (ISO 27874)
Clip	: Stainless steel	-
Notched nut	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Locking washer	: Bronze (UNS C52100)	Nickel plated (FS-QQ-N-290A)
Retaining ring	: PEEK	-
Other metallic part	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)
Contact wire	: Brass (UNS C27400)	Tinned
Position insert	: POM	-
Fixing resin	: Epoxy	-

Panel cut-out



Torque for
mounting
nut : 6 Nm

A-A cross-section (PCB drilling pattern)



Spanner for notched nut : DCH.91.201.PA

**Fixed socket , with two nuts , with keys (A) , with
elbow (90°) contact for PCB . (Back panel mounting) .
Series 2B , multipole (16)**

ETUDE N° E3127-E10817-E1406-E2173-E6158-E7157-E7213

Echelle

Dessiné	13.06.2007	OVU / RMO
Contrôle	15.07.2019	NHA / ATVI
Modif.	01	15.07.2019/ OVU



LEMO

LEMO SA
Chemin des Champs-Courbes 28
1024 Ecublens - SWITZERLAND

Tel. (+41 21) 695 16 00
email : info@lemo.com
www.lemo.com

ECA.2B.316.CLV