






Outer shell	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Earthing crown	: Bronze (UNS C54400)	Nickel plated (FS-QQ-N-290A)
Insulator	: PEEK	-
Female contact	: Bronze (UNS C54400)	Gold plated (ISO 4523)
Clip	: Stainless steel	-
Conical nut	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Locking washer	: Bronze (UNS C52100)	Nickel plated (FS-QQ-N-290A)
Retaining ring	: PEEK	-
Other metallic parts	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)
Contact wire	: Bronze (UNS C27400)	Tinned
Position insert	: POM	-
Fixing resin	: Epoxy	-

Panel cut-out



Torque for
mounting
nut : 9 Nm

A-A cross-section (PCB drilling pattern)



Fixed socket , with two nuts , with key (G) , with
elbow (90°) contact for PCB . (Back panel mounting) .
Series 3B , multipole (30)

ETUDE N°

Echelle

Dessiné 24.03.1998 FNI / ATA

Contrôle 15.06.2010 JPBA/ CDE

Modif. 02 15.06.2010/ OVU



LEMO

CH-1024 Ecublens

ECG.3B.330.CLV