




Outer shell	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Earthing crown	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)
Insulator	: PEEK	-
Female contact	: Bronze (UNS C54400)	Gold plated (ISO 27874)
Conical nut	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Locking washer	: Bronze (UNS C52100)	Nickel plated (FS-QQ-N-290A)
Other metallic parts	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)

Technical drawing of a hole in a plate. The hole has a diameter of $\phi 25.20^{+0.1}_0$. The plate has a thickness of $23.60^{+0.1}_0$. The hole is centered in the plate.

Fixed socket , with two nuts , with key (G) .
(Back panel mounting) .
Series 4B , multipole (10)

Echelle —	Dessiné	07.06.2018		OVU / NHA
	Contrôle	07.06.2018		NHA / ATVI
	Modif.	00	07.06.2018/ OVU	

