







Outer shell	: Brass (UNS C38500)	Chrome plated (SAE AMS 2460)
Earthing crown	: Brass (UNS C38500)	Nickel plated (SAE AMS QQ N 290)
Insulator	: PEEK	-
Conical nut	: Brass (UNS C38500)	Chrome plated (SAE AMS 2460)
Male contact	: Brass (UNS C38500)	Gold plated (ISO 27874)
Other metallic part	: Brass (UNS C38500)	Nickel plated (SAE AMS QQ N 290)
O-Rings	: Silicone (MVQ)	-

Panel cut-out



Torque for
mounting
nut : 12 Nm

PCB drilling pattern



**Fixed socket with nut fixing , with keys (L) .
for PCB . (Back panel mounting) .
Series 3K , multipole (26)**

ETUDE N° E1826

Echelle

Dessiné 03.09.2020 OVU / NHA

Contrôle 03.09.2020 NHA / CDE

Modif. 00 03.09.2020/ OVU



LEMO

LEMO SA
Chemin des Champs-Courbes 28
1024 Ecublens - SWITZERLAND

Tel. (+41 21) 695 16 00
email : info@lemo.com
www.lemo.com

EEL.3K.326.CLD