




Outer shell	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Earthing crown	: Bronze (UNS C54400)	Nickel plated (FS-QQ-N-290A)
Insulator	: PEEK	-
Female contact	: Bronze (UNS C54400)	Gold plated (ISO 27874)
Notched nut	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
O-rings	: Silicone (MVQ)	-

Technical drawing of a hole in a plate. The hole has a diameter of $\phi 9.10^{+0.1}_{-0}$. The plate has a thickness of $8.3^{+0.1}_{-0}$. The hole is centered in the plate.

Technical drawing of a part showing a 45° chamfer and a 90° hole pattern. The drawing includes dimensions: $\phi 0.50^{+0.1}$ (x4) and $\phi 2.5$.

10.10.2016 / OVU

