






Outer shell	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Earthing crown	: Cu-Be (UNS C17300)	Nickel plated (FS-QQ-N-290A)
Insulator	: PEEK	-
Locking washer	: Bronze (UNS C52100)	Nickel plated (FS-QQ-N-290A)
Other metallic parts	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)

Panel cut-out



Torque for
mounting
nut : 1 Nm

Spanner for nut : DCA.91.149.0TN or
Spanner for nut : DCG.91.149.0TN

Fixed socket , nut fixing , with key (G) , with extended
insulator for crimp contacts .

Series 00 , multipole (4) (Without contacts)

ETUDE N°

Echelle

Dessiné

14.12.1998

OVU /ATAB

Contrôle

04.10.2013

JPBA/ATVI

Modif.

02

04.10.2013/ OVU



LEMO

CH-1024 Ecublens

EGG.00.304.CYZ