






Outer shell	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Earthing crown	: Bronze (UNS C54400)	Nickel plated (FS-QQ-N-290A)
Insulator	: PEEK	-
Female contact	: Bronze (UNS C54400)	Gold plated (ISO 27874)
Locking washer	: Bronze (UNS C52100)	Nickel plated (FS-QQ-N-290A)
Other metallic part	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)
O-rings	: Silicone (MVQ)	-

Panel cut-out



Torque for
mounting
nut : 2.5 Nm

Spanner for nut : DCA.91.161.1TN or
Spanner for nut : DCG.91.161.1TN

**Fixed socket with nut fixing , with key (G) .
Series 0T , multipole (12)**

ETUDE N° E10425-E10715-E10536

Echelle —	Dessiné	23.06.2016	OVU / NHA
	Contrôle	23.06.2016	NHA / ATVI
	Modif.	00	23.06.2016/ OVU



LEMO

CH-1024 Ecublens

EGG.0T.312.CLL