






Outer shell	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Earthing crown	: Bronze (UNS C54400)	Nickel plated (FS-QQ-N-290A)
Insulator	: PEEK	-
Female contact	: Bronze (UNS C54400)	Gold plated (ISO 4523)
Locking washer	: Bronze (UNS C52100)	Nickel plated (FS-QQ-N-290A)
Other metallic parts	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)
Female coaxial contact	: (PSS.2B.250.ZTME30)	(See customer drawing)

Stripping dimensions



Panel cut-out



Torque for
mounting
nut : 9 Nm

Spanner for nut : DCA.91.282.2TN or
Spanner for nut : DCG.91.282.2TN

Fixed socket with nut fixing , with key (G) .

(Cable group 1)

Series 3B , 2coax50 Ω(typeC)+ 16LV(φ0.7)

ETUDE N° E1936-B

Echelle —	Dessiné	01.07.2002	BC / RMO
	Contrôle	04.11.2010	JPBA/ATVI
	Modif.	02	04.11.2010/ OVU



LEMO

CH-1024 Ecublens

EGG.3B.856.CLL1