







Outer shell	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Earthing crown	: Bronze (UNS C54400)	Nickel plated (FS-QQ-N-290A)
Insulator	: PEEK	-
Female contact	: Bronze (UNS C54400)	Gold plated (ISO 27874)
Locking washer	: Bronze (UNS C52100)	Nickel plated (FS-QQ-N-290A)
Other metallic part	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)
O-rings	: Silicone (MVQ)	-

Panel cut-out



Torque for
mounting
nut : 4.5 Nm

PCB drilling pattern



Spanner for nut : DCA.91.201.4 TN or
Spanner for nut : DCG.91.201.4 TN

**Fixed socket with nut fixing , with key (G) ,
for PCB .**

Series 1T , multipole (8)

ETUDE N° E10643

Echelle

Dessiné 20.05.2016 OVU / NHA

Contrôle 20.05.2016 NHA / ATVI

Modif. 00 20.05.2016/ OVU



LEMO

CH-1024 Ecublens

EGG.1T.308.CLN