



Outer shell	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Earthing crown	: Bronze (UNS C54400)	Nickel plated (FS-QQ-N-290A)
Insulator	: PEEK	-
Female contact	: Bronze (UNS C54400)	Gold plated (ISO 27874)
Locking washer	: Bronze (UNS C52100)	Nickel plated (FS-QQ-N-290A)
Other metallic parts	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)
Female coaxial contact	: (PSS.2B.250.ZTME31)	(See customer drawing)

Technical drawing of a cable assembly. The drawing shows a cross-section of a cable with a braided shield and an inner conductor. The dimensions are indicated as 3 ± 0.2 and 16 ± 0.5 .

Spanner for nut	: DCA.91.282.2TN or
Spanner for nut	: DCG.91.282.2TN

(Cable group 3)

Echelle —	Dessiné	07.02.2018		OVU / NHA
	Contrôle	07.02.2018		NHA / ATVI
	Modif.	00	07.02.2018/ OVU	

EGG.3B.856.CLL3