






|                      |                       |                              |
|----------------------|-----------------------|------------------------------|
| Outer shell          | : Brass (UNS C38500)  | Chrome plated (FS-QQ-C-320B) |
| Earthing crown       | : Bronze (UNS C54400) | Nickel plated (FS-QQ-N-290A) |
| Insulator            | : PEEK                | -                            |
| Female contact       | : Bronze (UNS C54400) | Gold plated (ISO 4523)       |
| Female fluidic tube  | : Brass (UNS C38500)  | Nickel plated (FS-QQ-N-290A) |
| Locking washer       | : Bronze (UNS C52100) | Nickel plated (FS-QQ-N-290A) |
| Other metallic parts | : Brass (UNS C38500)  | Nickel plated (FS-QQ-N-290A) |

Panel cut-out



Torque for  
mounting  
nut : 6 Nm

Spanner for nut : DCA.91.231.7TN or  
Spanner for nut : DCG.91.231.7TN

Fixed socket , with nut fixing , with key (G) ,  
Series 2B , 1fluidic(inner  $\phi 1.6$ ) + 6LV( $\phi 0.7$ )

ETUDE N° E1598

Echelle

—

|          |          |                |
|----------|----------|----------------|
| Dessiné  | 03.11.03 | OVU / RMO      |
| Contrôle | 03.11.03 | RMO / CDE      |
| Modif.   | 00       | 03.11.03 / OVU |



**LEMO**

CH-1024 Ecublens

**EGG.2B.013.CLL**