





Outer shell	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Earthing crown	: Bronze (UNS C54400)	Nickel plated (FS-QQ-N-290A)
Insulator	: PEEK	-
Female contact	: Bronze (UNS C54400)	Gold plated (ISO 27874)
Locking washer	: Bronze (UNS C52100)	Nickel plated (FS-QQ-N-290A)
Other metallic parts	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)
Female coaxial contact	: (PSS.2B.250.ZTME24)	(See customer drawing)

Stripping dimensions



Panel cut-out



Torque for
mounting
nut : 9 Nm

Spanner for nut : DCA.91.282.2TN or
Spanner for nut : DCG.91.282.2TN

Fixed socket with nut fixing , with key (G) .

(Cable group 2)

Series 3B , 1coax50Ω (typeC)+ 22LV(φ0.7)

ETUDE N° E1936

Echelle —	Dessiné	11.11.2019	OVU / NHA
	Contrôle	11.11.2019	NHA / CDE
	Modif.	00	11.11.2019 / OVU



LEMO

LEMO SA
Chemin des Champs-Courbes 28
1024 Ecublens - SWITZERLAND

Tel. (+41 21) 695 16 00
email : info@lemo.com
www.lemo.com

EGG.3B.822.CLL2