






Outer shell	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Earthing crown	: Bronze (UNS C54400)	Nickel plated (FS-QQ-N-290A)
Insulator	: PEEK	-
Female contact	: Bronze (UNS C54400)	Gold plated (ISO 4523)
Locking washer	: Bronze (UNS C52100)	Nickel plated (FS-QQ-N-290A)
Other metallic parts	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)

Panel cut-out



Torque for mounting nut : 6 Nm

Spanner for nut : DCA.91.231.7TN or
Spanner for nut : DCG.91.231.7TN

Fixed socket with nut fixing , with key (G) ,
visible shell .
Series 2B , multipole (18)

ETUDE N° E1491

Echelle

—

Dessiné	13.02.08	OVU / RMO
Contrôle	13.02.08	RMO / CDE
Modif.	00	13.02.08 / OVU



LEMO

CH-1024 Ecublens

EHG.2B.318.CLL