






Outer shell	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Earthing crown	: Bronze (UNS C54400)	Nickel plated (FS-QQ-N-290A)
Insulator	: PEEK	-
Female contact	: Bronze (UNS C54400)	Gold plated (ISO 27874)
Male contact	: Brass (UNS C38500)	Gold plated (ISO 27874)
Locking washer	: Bronze (UNS C52100)	Nickel plated (FS-QQ-N-290A)
Other metallic part	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)

Panel cut-out



Torque for
mounting
nut : 4.5 Nm

Spanner for nut : DCA.91.201.4 TN or
Spanner for nut : DCG.91.201.4 TN

**Fixed socket , with nut fixing , protruding shell .
Series 1S , multipole (2)**

ETUDE N° E1553-E7218

Echelle —	Dessiné	30.10.1997	FNI /ATAB
	Contrôle	22.01.2018	NHA /ATVI
	Modif.	01	22.01.2018/ OVU



LEMO

LEMO SA
Chemin des Champs-Courbes 28
1024 Ecublens - SWITZERLAND

Tel. (+41 21) 695 16 00
email : info@lemo.com
www.lemo.com

EHP.1S.302.CLL