






Outer shell	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Earthing crown	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)
Insulator	: PEEK	-
Female contact	: Bronze (UNS C54400)	Gold plated (ISO 4523)
Male contact	: Brass (UNS C38500)	Gold plated (ISO 4523)
Locking washer	: Bronze (UNS C52100)	Nickel plated (FS-QQ-N-290A)
Other metallic parts	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)

Panel cut-out



Torque for
mounting
nut : 6 Nm

Spanner for nut : DCA.91.231.7TN or
Spanner for nut : DCG.91.231.7TN

Fixed socket , with nut fixing .
Series 2S , multipole (5)

ETUDE N°

Echelle

—

Dessiné	31.08.00	OVU / RMO
Contrôle	31.08.00	RMO / JPBA
Modif.	00	31.08.00 / OVU



LEMO

CH-1024 Ecublens

ERA.2S.305.CLL