





Note: Minimum length of free thread to ensure mating with plug FVN

Outer shell	: Brass (UNS C38500)	Black chrome
Earthing crown	: Cu-Be (UNS C17300)	Nickel plated (FS-QQ-N-290A)
Insulators	: PEEK	-
Female contact	: Cu-Be (UNS C17300)	Gold plated (ISO 4523)
Male sleeve	: Brass (UNS C38500)	Gold plated (ISO 4523)
Special notched nut	: Brass (UNS C38500)	Black chrome
Earthing tags	: Brass (UNS C38500)	Gold plated (ISO 4523)

Panel cut-out



Torque for
mounting
nut : 1 Nm

Spanner for notched nut : DCB.91.455.0LN

**Fixed socket with special notched nut , with tags .
(Back panel mounting) .
Series 00 , triaxial (50Ω)**

ETUDE N° E2305

Echelle —	Dessiné	05.11.1996	DVO / RMO
	Contrôle	01.03.2012	JPBA / ATVI
	Modif.	01	01.03.2012 / OVU



LEMO

CH-1024 Ecublens

ELF.00.650.KLL