






Outer shell	: PSU	White
Earthing crown with tag	: Bronze (UNS C54400)	Gold plated (ISO 27874)
Insulator	: PEEK	-
Female contact	: Bronze (UNS C54400)	Gold plated (ISO 27874)
Locking washer	: Bronze (UNS C52100)	Nickel plated (FS-QQ-N-290A)
Other metallic part	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)

* Secure with an adhesive (Vibra-tite VTCS-6 clear, e.g.) .

Panel cut-out



Torque for mounting nut : 0.8 Nm *

Spanner for nut : DCA.91.231.7TN or
Spanner for nut : DCG.91.231.7TN

**Fixed socket with earthing tag , nut fixing ,
with keys (Y) .**

Series 2B , multipole (10)

ETUDE N° E2337-E10572

Echelle —	Dessiné	21.02.2018	OVU / NHA
	Contrôle	21.02.2018	NHA / ATVI
	Modif.	00	21.02.2018/ OVU



LEMO

LEMO SA
Chemin des Champs-Courbes 28
1024 Ecublens - SWITZERLAND

Tel. (+41 21) 695 16 00
email : info@lemo.com
www.lemo.com

ENY.2B.310.PLLB