






Outer shell	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Insulator	: PEEK	-
Male contact	: Brass (UNS C38500)	Gold plated (ISO 4523)
Locking washer	: Bronze (UNS C52100)	Nickel plated (FS-QQ-N-290A)
Other metallic parts	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)
Male coaxial contact	: (FFS.2B.250.ZTCE31)	(See customer drawing)

Stripping dimensions



Panel cut-out



Torque for
mounting
nut : 9 Nm

Spanner for nut : DCA.91.282.2TN or
Spanner for nut : DCG.91.282.2TN

Fixed plug , non-latching , nut fixing , with key (G) .

(Cable group 3)

Series 3B , 2coax50 Ω (typeC)+ 6LV(φ0.9)

ETUDE N° E1849-E1286A

Echelle	Dessiné	21.11.2013	OVU / JPBA
	Contrôle	21.11.2013	JPBA / ATVI
	Modif.	00	21.11.2013 / OVU



LEMO

CH-1024 Ecublens

FAG.3B.846.CLA3