






DANGER

Outer shell	: Brass (UNS C38500)	Chrome plated (SAE AMS 2460)
Earthing crown	: Brass (UNS C38500)	Nickel plated (SAE AMS QQ N 290)
Insulator	: PEEK	-
Female contact (LV+HV)	: Bronze (UNS C54400)	Gold plated (ISO 27874)
Male contact (LV)+(HV)	: Brass (UNS C38500)	Gold plated (ISO 27874)
Other insulating parts	: PEEK	-
Other metallic parts	: Brass (UNS C38500)	Nickel plated (SAE AMS QQ N 290)
O-rings	: Silicone (MVQ)	-
Label	: Polyester	Yellow

Panel cut-out



Torque for
mounting
nut : 12 Nm

Fixed socket , with nut fixing .
Series 3E , (2) HV(1.3) + (4) LV(1.3)

ETUDE N° E6041

Echelle —	Dessiné	25.02.2020	OVU / NHA
	Contrôle	25.02.2020	NHA / CDE
	Modif.	00	25.02.2020/ OVU



LEMO

LEMO SA
Chemin des Champs-Courbes 28
1024 Ecublens - SWITZERLAND

Tel. (+41 21) 695 16 00
email : info@lemo.com
www.lemo.com

ERA.3E.734.CJL