



Outer shell	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Insulator	: PEEK	-
Male contact	: Brass (UNS C38500)	Gold plated (ISO 4523)
Locking washer	: Bronze (UNS C52100)	Nickel plated (FS-QQ-N-290A)
Other metallic parts	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)

Panel cut-out



Torque for
mounting
nut : 6 Nm

Spanner for nut : DCA.91.231.7TN or
Spanner for nut : DCG.91.231.7TN

**Fixed plug , non-latching , nut fixing ,
with key (G) .
Series 2B , multipole (10)**

ETUDE N°

Echelle

—

Dessiné	14.02.02	OVU / RMO
Contrôle	20.08.07	RMO / CDE
Modif.	01	20.08.07 / OVU



LEMO

CH-1024 Ecublens

FAG.2B.310.CLA