



Outer shell	: Stainless steel (AISI304L)	-
Latch sleeve	: Stainless steel (AISI416)	-
Inner sleeve	: Stainless steel (AISI304L)	-
Front ring	: Stainless steel (AISI304L)	-
Cap	: Stainless steel (AISI304L)	-
Collet nut	: Stainless steel (AISI304L)	-
Insulator	: PEEK	-
Female contact	: Bronze (UNS C54400)	Gold plated (ISO 4523)
Clip	: Cu-Be (UNS C17200)	-
Clip	: Stainless steel (AISI416)	-
Glands	: EPDM	-
Lanyard release	: Stainless steel (AISI316)	-
Other outer metallic parts	: Stainless steel (AISI304)	-
Other inner metallic parts	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)
O-rings	: EPDM	-
Marking strip	: Epoxy paint	Black

Crimping tool	: DPC.91.101.A
Extractor	: DCC.91.202.5LA
Female contact	: EGG.5B.675.ZZM
Female positioner	: DCE.91.205.BVCM

**Elbow plug (120°) with positioning pin , with cable clamps  
rough narrow handling surface and with lanyard release .  
Series 5N , multipole (14)**

ETUDE N° E6225

Echelle	Dessiné	18.07.2013	OVU /JPBA
	Contrôle	18.07.2013	JPBA/ATVI
	Modif.	00	18.07.2013/ OVU



**LEMO**

CH-1024 Ecublens

**FMG.5N.314.TLMY\_\_**