





Outer shells	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Latch sleeve	: Special brass	Chrome plated (FS-QQ-C-320B)
Inner shell	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)
Front ring	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Collet nut	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Insulator	: PEEK	-
Other metallic parts	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)
O-ring	: Viton (FPM)	-

Panel cut-out



Parts that must be ordered separately :

Fiber-optic contact ref : FFS.F2.BB2.LCT10 or ...E30 ferrule hole 126µm
Fiber-optic contact ref : FFS.F2.BA2.LCT10 or ...E30 ferrule hole 125µm

Assembly instruction per document n°__

**Straight plug , round flange , with key (G) ,
4 holes fixing .**

Series 5K , 12F0(typeF2)

ETUDE N° E2592-E10352

Echelle —	Dessiné	05.06.2012	OVU / JPBA
	Contrôle	05.06.2012	JPBA / ATVI
	Modif.	00	05.06.2012/ OVU



LEMO

CH-1024 Ecublens

FXG.5K.03L.CLZ