





Outer shell	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Earthing crown	: Bronze (UNS C54400)	Gold plated (ISO 27874)
Insulator	: PTFE	-
Female contact	: Bronze (UNS C54400)	Gold plated (ISO 27874)
Earthing washer	: Brass (UNS C27400)	CuZn alloy
Other metallic parts	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)
Sealing resin	: Epoxy	-
O-rings	: Silicone (MVQ)	-

Stripping dimensions



Slide a piece of heat shrink tubing (1 (not supplied) of the correct length over the dielectric of the remaining cable .
Slide the heat shrink tubing onto the solder barrel of the contact . With a heat gun fully shrink the tubing until full melting of the inner adhesive coating .
Solder the braid onto the earthing washer.

Echelle —	Dessiné	19.12.2017		OVU / NHA
	Contrôle	19.12.2017		NHA / ATVI
	Modif.	00	19.12.2017 / OVU	

