





Outer shell	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Earthing crown	: Bronze (UNS C54400)	Nickel plated (FS-QQ-N-290A)
Collet nut	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Insulator	: PEEK	-
Notched nut	: Brass (UNS C38500)	Chrome plated (FS-QQ-C-320B)
Locking washer	: Bronze (UNS C52100)	Nickel plated (FS-QQ-N-290A)
Other metallic parts	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)

Panel cut-out



Torque for
mounting
nut : 2.5 Nm

Assembly instruction per customer drawing : PFG.0B.306.CYMD__

**Straight socket , with two nuts , with key (G) , without
collet , with extended insulator for crimp contact .
Series 0B , multipole (6) (without contacts)**

ETUDE N°

Echelle

Dessiné

04.11.98

XKO / JCHU

Contrôle

27.05.05

RMO / CDE

Modif.

01

27.05.05 / OVU



LEMO

CH-1024 Ecublens

PFG.0B.306.CYZZ