







Outer shell	: Aluminium (AA 6262A) or (AA 6023)	Anthracite nickel
Earthing crown	: Bronze (UNS C54400)	Gold plated (ISO 27874)
Insulator	: PEEK	-
Female contact	: Bronze (UNS C54400)	Gold plated (ISO 27874)
Conical nut	: Aluminium (AA 6262A) or (AA 6023)	Anthracite nickel
Ground pin	: Stainless steel (AISI303)	Gold plated (ISO 27874)
Sealing resin	: Epoxy	-
O-rings	: Viton (FPM)	-

Panel cut-out



Torque for mounting nut : 1.5 Nm

PCB drilling pattern



Spanner for conical nut
Insert for conical nut

: DCM.65.000.4PA
: DCM.65.160.AZ

Fixed socket , nut fixing , with keys (N) , watertight , for PCB . (Back panel mounting) . Series 1M , multipole (8)

ETUDE N° E6361-E6341-E11355

Echelle

Dessiné

14.01.2008

OVU / RMO

Contrôle

03.02.2021

NHA / CDE

Modif.

02

03.02.2021/ OVU



LEMO

LEMO SA
Chemin des Champs-Courbes 28
1024 Ecublens - SWITZERLAND

Tel. (+41 21) 695 16 00
email : info@lemo.com
www.lemo.com

HEN.1M.308.XLNP