



Female sleeve	: Bronze (UNS C54400)	Gold plated (ISO 27874)
Insulator	: PEEK	-
Male contact	: Brass (UNS C38500)	Gold plated (ISO 27874)
Crimping collet	: Brass (UNS C38500)	Gold plated (ISO 27874)
Other insulating part	: PEEK	-
Crimp ferrule	: Cu (UNS C18700)	Gold plated (ISO 27874)

- Slide the cable into the crimp ferrule ① Strip according to the given dimensions .
- Winden the screen , slide the crimping collet ② fully onto the cable until the insulator touches the dielectric and one can see the conductor in the contact ③ hole . Solder the contact .
- Slide the crimp ferrule fully onto the screen until it touches the crimping collet . Crimp with crimping tool .
- Slide the coax female contact ④ into the socket insulator ⑤ front and the premounted cable assembly ⑥ into the insulator back .
- Screw the coax female contact with the female spanner ⑦ on the collet (verify that the four small guides fit well into the slots of the female contact) by holding it with the flat spanner SW2,2 of the installation tool . Tighten to the maximum torque value of 0,1 Nm .

Crimping dimension	Crimping tool with dies	: DPE.99.002.5K
	Installation tool	: DCC.91.050.2LA
	Crimp ferrule	: FFS.1B.160.DA
	For cable	: RG.178B/U (50Ω)

**Female coaxial contact , type E ,  
for cable crimping . (Cable group 2)  
For series 2B , coaxial (50Ω)**

ETUDE N° E6185-E4057-E2391

Echelle	Dessiné	04.02.1994	XK0 / GJE
	Contrôle	04.05.2018	NHA / ATVI
	Modif.	04	04.05.2018/ OVU