



Outer shells	: Stainless steel (AISI304L)	-
Earthing crown	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)
Retaining ring	: Stainless steel (AISI304L)	-
Collet nut	: Stainless steel (AISI304L)	-
Insulator	: PEEK	-
Male contact (LV)	: Brass (UNS C34500)	Gold plated (ISO 4523)
Female contact (Power)	: Bronze (UNS C54400)	Gold plated (ISO 4523)
Clips	: Cu-Be (UNS C17200)	-
Cable anchor + screws	: Stainless steel	-
Crimping tube	: Copper (UNS C18700)	Nickel plated (FS-QQ-N-290A)
Other metallic parts	: Brass (UNS C38500)	Nickel plated (FS-QQ-N-290A)
Lip seal	: Silicone (MVQ)	-
O-rings	: Silicone (MVQ)	-
Heat shrink tubing	: Polyolefin	Black
Male contact (FO)	: (FFS.F2.BA2.LCE30)	(See customer drawing)

Assembly instruction per document n° __

Free socket , with keys (W) , cable collet adapter and fitting a bend relief with cap . (Enhanced screen efficiency)
Series 3K , 2FO(typeF2) + 2LV(Ø0.9) + 2power(Ø1.3)

ETUDE N° E6242C-E9084

Echelle —	Dessiné	30.04.2014	OVU /JPBA
	Contrôle	30.04.2014	JPBA/ATVI
	Modif.	00	30.04.2014/ OVU



LEMO

CH-1024 Ecublens

PUW.3K.93C.TLEC96